


## ActivaScrew™ Cannulated – Innowacyjna kaniulowana śruba kompresyjna



### Opis produktu:

ActivaScrew™ Cannulated - jest biochłaniającym implantem zbudowanym z 4 generacji ko-polimeru (PLGA). Na chwilę obecną firma Bioretec™ jest jedynym producentem implantów w zaawansowanym procesie technologicznym umożliwiającym produkcję implantu w postaci PLGA 4 generacji.

### Zdjęcia produktu:



### Szczegółowy opis produktu:

## ActivaScrew™ Cannulated – Innowacyjna kaniulowana śruba kompresyjna

Kaniulowane śruby ActivaScrew™ Cannulated oprócz innowacyjnej technologii produkcji implantu z ko-polimeru PLGA posiadają opatentowaną technologię Auto Compression™.

[img-10013-left-home\_default]

### Cechy implantu ActivaScrew™ Cannulated:

- brak odczynów zapalnych, dzięki opatentowanej budowie ko-polimeru PLGA
- wysoka wytrzymałość
- intuicyjna i bezpieczna metoda zakładania
- bioresorpcja implantu po ok. 2 latach
- doskonałe wyniki kliniczne (prowadzona baza wyników klinicznych przez firmę)
- po wszczęciu zapewnia przez 8 tygodni zamierzoną funkcjonalność
- opatentowany kształt implantu zapewniający natychmiastowe blokowanie w miejscu wszczęcia
- opatentowana technologia „Auto Compression™” zapobiegająca obłuzowaniu się implantu

po wszczępie

- technologia „Auto Compression™” po wszczępie w ludzkiej tkance automatycznie zacieśnia implant z autonomiczną kontrakcją implantu (maksymalnie 1-2% całkowitej wielkości implantu)
- nie wymaga specjalnego instrumentarium (standard AO)
- dzięki technologii „Auto Compresion™” spełniają rolę standardowych śrub typu Herbert
- szeroki wybór śrub z pełnym gwintem jak i częściowym gwintem

### **Procedury w których wykorzystywany jest implant ActivaScrew™ Cannulated:**

- osteotomie
- reinsertcja odłamów kostnych
- reinsertcja odłamów kostno-chrzęstnych (OCD)
- mocowanie graftów kostnych
- zabieg więzozrostu piszczelowo-strzałkowego (syndesmosis)

[img-10016-left-large\_default]

### **Szeroki wybór rozmiaru i typu implantu ActivaScrew™ Cannulated:**

#### **Śruby ActivaScrew™ Cannulated z pełnym gwintem:**

B-ASC-3520	ActivaScrew™ Cannulated 3.5 x 20 mm
B-ASC-3524	ActivaScrew™ Cannulated 3.5 x 24 mm
B-ASC-3528	ActivaScrew™ Cannulated 3.5 x 28 mm
B-ASC-3532	ActivaScrew™ Cannulated 3.5 x 32 mm
B-ASC-3536	ActivaScrew™ Cannulated 3.5 x 36 mm
B-ASC-3540	ActivaScrew™ Cannulated 3.5 x 40 mm
B-ASC-4040	ActivaScrew™ Cannulated 4.0 x 40 mm
B-ASC-4045	ActivaScrew™ Cannulated 4.0 x 45 mm
B-ASC-4050	ActivaScrew™ Cannulated 4.0 x 50 mm
B-ASC-4055	ActivaScrew™ Cannulated 4.0 x 55 mm
B-ASC-4060	ActivaScrew™ Cannulated 4.0 x 60 mm
B-ASC-4065	ActivaScrew™ Cannulated 4.0 x 65 mm
B-ASC-4070	ActivaScrew™ Cannulated 4.0 x 70 mm
B-ASC-4080	ActivaScrew™ Cannulated 4.0 x 80 mm
B-ASC-4090	ActivaScrew™ Cannulated 4.0 x 90 mm
B-ASC-4540	ActivaScrew™ Cannulated 4.5 x 40 mm
B-ASC-4550	ActivaScrew™ Cannulated 4.5 x 50 mm

B-ASC-4560	ActivaScrew™ Cannulated 4.5 x 60 mm
B-ASC-4570	ActivaScrew™ Cannulated 4.5 x 70 mm
B-ASC-4580	ActivaScrew™ Cannulated 4.5 x 80 mm
B-ASC-4590	ActivaScrew™ Cannulated 4.5 x 90 mm

### Śruby ActivaScrew™ Cannulated z częściowym gwintem:

B-ALC-3524	ActivaScrew™ Cannulated LAG 3.5 x 24 mm, thread 10 mm
B-ALC-3526	ActivaScrew™ Cannulated LAG 3.5 x 26 mm, thread 12 mm
B-ALC-3528	ActivaScrew™ Cannulated LAG 3.5 x 28 mm, thread 12 mm
B-ALC-3530	ActivaScrew™ Cannulated LAG 3.5 x 30 mm, thread 14 mm
B-ALC-3535	ActivaScrew™ Cannulated LAG 3.5 x 35 mm, thread 14 mm
B-ALC-3540	ActivaScrew™ Cannulated LAG 3.5 x 40 mm, thread 14 mm
B-ALC-3545	ActivaScrew™ Cannulated LAG 3.5 x 45 mm, thread 15 mm
B-ALC-4035	ActivaScrew™ Cannulated LAG 4.0 x 35 mm, thread 18 mm
B-ALC-4040	ActivaScrew™ Cannulated LAG 4.0 x 40 mm, thread 20 mm
B-ALC-4045	ActivaScrew™ Cannulated LAG 4.0 x 45 mm, thread 22 mm
B-ALC-4050	ActivaScrew™ Cannulated LAG 4.0 x 50 mm, thread 24 mm
B-ALC-4055	ActivaScrew™ Cannulated LAG 4.0 x 55 mm, thread 26 mm
B-ALC-4060	ActivaScrew™ Cannulated LAG 4.0 x 60 mm, thread 28 mm
B-ALC-4065	ActivaScrew™ Cannulated LAG 4.0 x 65 mm, thread 30 mm
B-ALC-4070	ActivaScrew™ Cannulated LAG 4.0 x 70 mm, thread 32 mm
B-ALC-4080	ActivaScrew™ Cannulated LAG 4.0 x 80 mm, thread 40 mm
B-ALC-4090	ActivaScrew™ Cannulated LAG 4.0 x 90 mm, thread 46 mm
B-ALC-4540	ActivaScrew™ Cannulated LAG 4.5 x 40 mm, thread 20 mm
B-ALC-4545	ActivaScrew™ Cannulated LAG 4.5 x 45 mm, thread 22 mm
B-ALC-4550	ActivaScrew™ Cannulated LAG 4.5 x 50 mm, thread 24 mm
B-ALC-4555	ActivaScrew™ Cannulated LAG 4.5 x 55 mm, thread 26 mm
B-ALC-4560	ActivaScrew™ Cannulated LAG 4.5 x 60 mm, thread 28 mm

B-ALC-4565	ActivaScrew™ Cannulated LAG 4.5 x 65 mm, thread 30 mm
B-ALC-4570	ActivaScrew™ Cannulated LAG 4.5 x 70 mm, thread 32 mm
B-ALC-4580	ActivaScrew™ Cannulated LAG 4.5 x 80 mm, thread 40 mm
B-ALC-4590	ActivaScrew™ Cannulated LAG 4.5 x 90 mm, thread 46 mm

**Informacje:****Model:**